

25mW, 532nm DPSS Pointing Laser



DPSS Pointing Lasers

Stock #19-470 3-4 DAYS

-

1

+

£437.75

ADD TO CART

Qty 1-9

£437.75

Qty 10+

£394.40

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Operating Temperature (°C):
23 to 27

Operating Voltage (V):
3

Output Power (mW):
25

Spatial Mode: TEM ₀₀
Wavelength (nm): 532.00 ±1
Wavelength Tolerance (nm): ±1
Power Supply: Power Supply Required and Sold Separately: USA: #19-475 Europe: #19-475 Japan: Not Available Korea: Not Available China: #19-475
Modulation Frequency (kHz): Not Modulated
Note: Compatible TEC Controller (#19-476) sold separately
Beam Diameter (mm): 1.5 Typical
Beam Divergence (mrad): <1.5 Typical
Laser Class - CDRH: IIIb
Color: Green
Length (mm): 90.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant