

## 2.62", English Rotary Stage



Stock #38-193 CLEARANCE 2 In Stock

⊖ 1 ⊕ £1,120<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	£1,120.00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

English **Type:**

### Physical & Mechanical Properties

Rotary **Type of Movement:**

Ball Bearing **Guide System:**

66.5 x 66.5 **Stage Size (mm):**

±5 (Fine), 360 (Coarse)	<b>Travel (°):</b>
0.50" Dia. Thru	<b>Center Hole:</b>
Aluminum top and base; steel tangent arm drive	<b>Construction:</b>
12	<b>Increments (arcmin):</b>
10	<b>Load Capacity, Normal (lbs):</b>
4	<b>Load Capacity, Vertical (lbs):</b>
2.62 x 2.62	<b>Stage Size (inches):</b>
1.8	<b>Weight (lbs):</b>
2.62	<b>Table Diameter (inches):</b>

## Hardware & Interface Connectivity

Tangent Arm	<b>Type of Drive:</b>
-------------	-----------------------

## Threading & Mounting

(4) 6-32 on 1.125" dia. B.C., (4) 1/4-20 on 2.00" dia. B.C.	<b>Mounting Threads:</b>
---	--------------------------

## Regulatory Compliance

Compliant	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>

## Product Details

- Low Wear, Low Friction Movement with Coarse or Fine Adjustment
  - 2 or 2.62" Diameter Stages with Tapped Mounting Holes
  - Calibrated Dial with 12 Minute Vernier for Accurate Read-Out
- Compact miniature stages provide low-friction rotary movement with both coarse and fine adjustment. This allows for quick rotation over a continuous 360° travel, plus precise angular adjustment at any selected position. Features include preloaded angular contact ball bearing system, a positive position lock, a 2.00" or 2.62" diameter stage with tapped mounting holes and a calibrated dial with six minute vernier for accurate positional read-out. It can be combined with our compatible linear translation stages for multi-axis linear-rotary applications.

## Technical Information

