

2.62", English Rotary Stage



Stock #38-193 **2 In Stock**

-

1

+

£1,120^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	£1,120.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

English

Type:

Physical & Mechanical Properties

1.8

Weight (lbs):

66.5 x 66.5

Stage Size (mm):

2.62 x 2.62

Stage Size (inches):

Construction: Aluminum top and base; steel tangent arm drive	
Center Hole: 0.50" Dia. Thru	
Travel (°): ±5 (Fine), 360 (Coarse)	
Increments (arcmin): 12	
Load Capacity, Normal (lbs): 10	
Load Capacity, Vertical (lbs): 4	
Type of Movement: Rotary	
Guide System: Ball Bearing	
Table Diameter (inches): 2.62	

Hardware & Interface Connectivity

Type of Drive: Tangent Arm	
--	--

Threading & Mounting

Mounting Threads: (4) 6-32 on 1.125" dia. B.C., (4) 1/4-20 on 2.00" dia. B.C.	
---	--

Regulatory Compliance

RoHS 2015: Compliant	
Certificate of Conformance: View	

Product Details

- Low Wear, Low Friction Movement with Coarse or Fine Adjustment
 - 2 or 2.62" Diameter Stages with Tapped Mounting Holes
 - Calibrated Dial with 12 Minute Vernier for Accurate Read-Out
- Compact miniature stages provide low-friction rotary movement with both coarse and fine adjustment. This allows for quick rotation over a continuous 360° travel, plus precise angular adjustment at any selected position. Features include preloaded angular contact ball bearing system, a positive position lock, a 2.00" or 2.62" diameter stage with tapped mounting holes and a calibrated dial with six minute vernier for accurate positional read-out. It can be combined with our compatible linear translation stages for multi-axis linear-rotary applications.

Technical Information

