

270mm FL, 1064nm Edmund Optics® F-Theta Lens



Stock #15-183 3-4 DAYS

- 1 + **£952.85**

ADD TO CART

Qty 1-4
£952.85
Qty 5+
£857.65
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):
1064

Focal Length FL (mm):
273.20

Maximum Diameter (mm):
106

Scan Angle (°):

±24.10
Scan Field (mm): 164.0 x 164.0
Mounting Threads: M85 x 1.0
Telecentricity (°): Not Specified
Transmission (%): ≥95
Type: F-Theta Lens
Working Distance (mm): 313.0
Wavelength Range (nm): 1064
Range Distance (mm): 352.5
Focus Size Diameter, 1/e² (μm): 31
Input Beam Diameter, 1/e² (mm): 12
Maximum Length (mm): 73.2

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View