

## 29mm Outer Dia., Zero Aperture, Burnished Steel Leaves



Zero Series

Stock **#57-588** □ **In Stock**

⊖ 1 ⊕ **£83.30**

ADD TO CART

|         |
|---------|
| Qty 1-4 |
| £83.30  |

|        |
|--------|
| Qty 5+ |
| £73.44 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

### Get Product Downloads

Minimum Aperture (mm):  
0.00

Maximum Aperture (mm):  
15.0

Outer Diameter (mm):  
29.0

|                                                                   |
|-------------------------------------------------------------------|
| <b>Construction:</b><br>Anodized Aluminum Alloy, Burnished Leaves |
| <b>Full Angular Range of Lever (°):</b><br>97.00                  |
| <b>Lever Diameter (mm):</b><br>3.00                               |
| <b>Lever Length (mm):</b><br>12.00                                |
| <b>Lever Position (mm):</b><br>2.50                               |
| <b>Number of Leaves:</b><br>Two sets of 6                         |
| <b>Operating Temperature (°C):</b><br><250                        |
| <b>Pin Thread &amp; Pitch:</b><br>M1.4 x 0.30mm                   |
| <b>Thickness (mm):</b><br>5.00                                    |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Compliant</a>             |