

## 2° Commercial Grade Wedge Prism



Stock #27-677 CLEARANCE 3-4 DAYS

- 1 + **£21.21**

ADD TO CART

|        |
|--------|
| Qty 1+ |
| £21.21 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

### Get Product Downloads

**Coating:**  
MgF<sub>2</sub> (400-700nm)

**Angle Tolerance (arcmin):**  
1.00

**Coating Specification:**  
R<sub>avg</sub> ≤1.75% @400 - 700nm

**Diameter (mm):**  
25.00 ±0.1

**Image Orientation:**  
Beam Deviation

|                                                              |
|--------------------------------------------------------------|
| <div>Power (diopters):<br/>3.49</div>                        |
| <div>Substrate: <div><div></div><div>N-BK7</div></div></div> |
| <div>Surface Accuracy:<br/>1λ</div>                          |
| <div>Thickness (mm):<br/>3.00</div>                          |
| <div>Type:<br/>Wedge Prism</div>                             |
| <div>Wedge Angle:<br/>3° 52'0"</div>                         |
| <div>Wedge Angle Deviation (°):<br/>2.00</div>               |

Regulatory Compliance

|                                                 |
|-------------------------------------------------|
| <div>RoHS:<br/>Compliant</div>                  |
| <div>Certificate of Conformance:<br/>View</div> |