

2° Commercial Grade Wedge Prism



Stock **#27-677** CLEARANCE 3-4 DAYS

- 1 + **£21.21**

ADD TO CART

Qty 1+
£21.21

Volume Pricing
Request Quote

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating:
MgF₂ (400-700nm)

Angle Tolerance (arcmin):
1.00

Coating Specification:
R_{avg} ≤1.75% @400 - 700nm

Diameter (mm):
25.00 ±0.1

Image Orientation:
Beam Deviation

Power (diopters):
3.49

Substrate: ☐
[N-BK7](#)

Surface Accuracy:
1λ

Thickness (mm):
3.00

Type:
Wedge Prism

Wedge Angle:
3° 52'0"

Wedge Angle Deviation (°):
2.00

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)