

TECHSPEC® 2" Dia, 4" FL Uncoated, Spherical Mirror



Stock **#32-814** [CONTACT US](#)

- 1 + **£102.00**

ADD TO CART

Qty 1-9
£102.00

Qty 10+
£86.70

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Substrate: ☐ BOROFLOAT®

Focal Length Tolerance (%): ±2

Surface Quality: 60-40

Surface Accuracy: λ/4
Diameter (inches): 2.0
Diameter (mm): 50.80 +0.5/-0
Diameter Tolerance (inches): +0.02/-0
Effective Focal Length EFL (inches): 4.00
Effective Focal Length EFL (mm): 101.60
Radius of Curvature (mm): 203.20
Aperture (f/#): f/2
Coating: Uncoated
Coating Type: Uncoated
Back Surface: Ground
Edge Thickness ET (inches): 0.50
Edge Thickness ET (mm): 12.70
Edge Thickness Tolerance (%): +0.0/-15
Type: Spherical Mirror

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View