

TECHSPEC®

2" Dia. Protected Silver, λ /10 Flat ZERODUR®



Stock #32-199-577

3-4 DAYS

-

1

+

£282.20

ADD TO CART

Qty 1-10

£282.20

Qty 11+

£254.15

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):

λ /10 (measured before coating)

Back Surface:

Commercial Polish

Surface Quality: 60-40
Diameter (mm): 50.80 +0.0/-1.0
Substrate: 
Coating Specification: R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Clear Aperture CA (mm): 45.72
Note: Flatness is specified as Peak to Valley
Thickness (mm): 12.70 ±1.5
Thickness Tolerance (mm): ±1.5
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 10
Wavelength Range (nm): 450 - 10000
Damage Threshold, Reference:  0.5 J/cm ² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant