

30° Full Fan Angle Laser Line Generator Lens



Powell Lenses

Stock **#43-473** 3-4 DAYS



1



£198.05

ADD TO CART

Qty 1-5

£198.05

Qty 6+

£158.53

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
8.90 +0.00/-0.15

Substrate: ☐
[N-BK7](#)

Coating:
VIS-NIR (450-900nm)

Type: Beam Shaping Lens
Wavelength Range (nm): 450 - 900
Coating Specification: BBAR @ 450 - 900nm
Height (mm): 8.90 +0.00/-2.00
Index of Refraction n_d : 1.517
Fan Angle (°): 30.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View