

3.0 OD M58 x 0.75, Machine Vision Absorptive ND Filter



Stock #21-738

CONTACT US

-

1

+

£105.40

ADD TO CART

Qty 1-9
£105.40
Qty 10+
£100.38
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Optical Density OD (Average):
3.0

Clear Aperture CA (mm):
53.00

Filter Thread:
M58 x0.75

Substrate:

ND Filter Glass
Surface Quality: 40-20
Transmission (%): 0.10
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
