

3.00" x 3.00", 6.0" FL, Cylinder Fresnel Lens



Cylinder Fresnel Lenses

Stock **#43-033** **4 In Stock**

⊖ 1 ⊕ £42⁴⁰

ADD TO CART

Volume Pricing

Qty 1-10	£42.40 each
Qty 11-49	£38.40 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Fresnel Lens **Type:**

Physical & Mechanical Properties

0.06 **Center Thickness CT (inches):**

±0.05 **Dimensional Tolerance (inches):**

3.0 x 3.0 **Dimensions (inches):**

76.2 x 76.2 **Dimensions (mm):**

3.0 x 3.0 **Effective Size (inches):**

±0.020 **Thickness Tolerance (inches):**

Optical Properties

152.40 **Effective Focal Length EFL (mm):**

Acrylic **Substrate:**

Uncoated **Coating:**

400 - 1100 **Wavelength Range (nm):**

6.00 **Effective Focal Length EFL (inches):**

65.00 **Groove Density (grooves/inch):**

1.49 **Index of Refraction (n_d):**

85 (Typical) **Transmission (%):**

Environmental & Durability Factors

80 (Maximum) **Operating Temperature (°C):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 242:**

Product Details

- Collapsed Version of a Standard Cylinder Lens
- Ideal for Focusing One Dimension
- Various Sizes Available

Technical Information

