

TECHSPEC® 30mm, Center Drive, Standard Top, 0.25" Travel, English Micrometer



Stock #83-503 **20+ In Stock**

- 1 + £350⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-2	£350.40 each
Qty 3+	£305.60 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

English Type:

Physical & Mechanical Properties

Linear (X) Type of Movement:

Crossed Roller Bearing Guide System:

30mm Standard-Top Stages - Center Drive



30mm Standard-Top Stages - Side Drive



40mm Standard-Top Stages - Center Drive



40mm Standard-Top Stages - Side Drive



70mm Standard-Top Stages - Center Drive



70mm Standard-Top Stages - Side Drive



125mm Standard-Top Stages - Center Drive



125mm Standard-Top Stages - Side Drive

