

TECHSPEC®

30mm, Side Drive, Thru-Hole, 0.5" Travel, Metric Stage



30mm, Side Drive, Thru-Hole, 0.5" Travel Stage

Stock #66-400

3-4 DAYS

-

1

+

£273.70

ADD TO CART

Qty 1-2

£273.70

Qty 3+

£238.76

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive:
Lead Screw

Drive Orientation: Side Drive
Type: Metric
Stage Size (mm): 30 x 30
Travel (mm): 13
Center Hole: 5/16"-24
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 3
Mounting Threads: (1) 5/16"-24, (6) M2 x 0.4
Stage Size (inches): 1.18 x 1.18
Straight Line Accuracy (µm): 2
Pitch (arcsec): 30
Yaw (arcsec): 25

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
