

TECHSPEC®

30R/70T NIR, C-Mounted Plate Beamsplitter



Stock **#49-687** [CONTACT US](#)



1



£250.75

ADD TO CART

Qty 1-4

£250.75

Qty 5+

£220.15

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating Specification:
Surface 2: Multi-Layer Anti-Reflection for Near-Infrared Region

Construction:
Plate

Dimensional Tolerance (mm):
+0.0/-0.25

Extension Length (mm): 38.0
Housing: Black Anodized Aluminum
Housing Dimension: 38 x 38 x 50
Mount: C-Mount Enclosure
Reflection/Transmission Ratio (R/T): 30/70
Reflection/Transmission Tolerance (%): ±5
Substrate: ☐ N-BK7
Surface Flatness (P-V): 1λ
Surface Quality: 60-40
Thread Type: C-Mount (1" x 32 TPI)
Type: Standard Beamsplitter
Wavelength Range (nm): 700 - 1100
Beamsplitter Included: #49-753

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View