

TECHSPEC[®] 355 & 532nm, 12.5mm Dia., OD 6.0 Multi-Notch Filter



TECHSPEC OD 6.0 Multi-Notch Filters for Nd:YAG Lasers

Stock **#87-015** 3-4 DAYS

[Additional Bandwidths](#)



1



£529.55

ADD TO CART

Qty 1-5

£529.55

Qty 6+

£423.72

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.00/-0.10

Optical Density OD (Average):
≥6.0

Center Wavelength CWL (nm):

355.00 & 532
Full Width-Half Max FWHM (nm): 10.00 @ 355nm 25 @ 532nm
Coating: Hard Coated
Surface Quality: 60-40
Thickness (mm): 3.50
Thickness Tolerance (mm): ±0.1
Transmission (%): >80 avg @ 325 - 400nm >90 avg @ 400 - 1200nm
Transmission Wavelength (nm): 325 - 1200
Type: Notch Filter
Construction: Mounted in Black Anodized Ring
Clear Aperture (%): >85
Durability: ML-C-48497A
Reflection at CWL (%): >99.5
Transmitted Wavefront, RMS: 1λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant