

365nm CWL, 10nm FWHM, 50mm Mounted Diameter



Stock **#86-997** CLEARANCE ☐ In Stock

-

1

+

£226.06

ADD TO CART

Qty 1+
£226.06

Volume Pricing
Request Quote

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm): 50.00 +0.0/-0.2
Angle of Incidence (°): 0
Optical Density OD (Average): ≥3.0
Clear Aperture CA (mm): 42.0

Center Wavelength CWL (nm): 365.00 ±2
Center Wavelength CWL Tolerance (nm): ±2
Full Width-Half Max FWHM (nm): 10.00 ±2
Full Width-Half Max FWHM Tolerance (nm): ±2
Minimum Transmission (%): ≥25
Operating Temperature (°C): -50 to +75
Coating: Traditional Coated
Surface Quality: 80-50
Thickness Tolerance (mm): ±0.1
Type: Bandpass Filter
Typical Applications: Hg Emission/Ar Laser Line
Blocking Wavelength Range (nm): 200 - 1200
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 7.5 ±0.1

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View