

TECHSPEC®

25.4mm Dia. x 150.0mm FL, VIS 0°, Inked, Plano-Convex Lens



Stock **#38-323-INK** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

£43.77

ADD TO CART

Qty 1-9
£43.77
Qty 10+
£39.31
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40 ±0.025

Effective Focal Length EFL (mm):

150.00 @587.6nm
Back Focal Length BFL (mm): 148.02
Coating: VS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.00 ±0.10
Edge Thickness ET (mm): 1.95
Radius R₁ (mm): 77.52
Clear Aperture CA (mm): 24.4
f/#: 5.91
Numerical Aperture NA: 0.08
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 425 - 675
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View