

[See all 31 Products in Family](#)

12-pin Hirose I/O Cable, 3m (for Manta, Prosilica GT/GC, Guppy Pro and Stingray Series)

See More by [Allied Vision](#)



#63-757



Stock **#63-757** 15 In Stock

-

1

+

£44⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£44.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Camera Accessory

Type:

Regulatory Compliance

[Compliant](#)

RoHS 2015:

View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- Rugged PoE (Power Over Ethernet) Cameras for Extreme Environments
- Precise (P-Iris) and DC Auto Iris Control
- Up to 31.4 MegaPixel Resolution
- C-Mount, F-Mount, and TFL-Mount Options


Allied Vision Prosilica GT Series GigE Cameras are designed for the harshest environments and fluctuating light conditions. Capable of operating in extreme temperatures ranging from -20° to 60°C, Allied Vsion Prosilica GT Series GigE Cameras are ideal for ITS and traffic imaging, machine vision, industrial inspection, security, or surveillance applications. Allied Vision Prosilica GT Series GigE Cameras feature both P-Iris and DC auto iris control for maintaining image quality, and support power over Ethernet for easy implementation.

Note: PoE Injector ([#68-469](#)) or power supply and GigE cable, such as [#63-431](#), are required for operation.

Technical Information

12-pin I/O connector

Bonito PRO, Goldeye and Goldeye Pro, Manta, and Prosilica GT

Type HR10A-10P-12S	Pin	Color	Pin	Color
	1	Blue	7	Brown
	2	Red	8	White
	3	Violet	9	Black
	4	Gray	10	Orange
	5	Yellow	11	White/Black
	6	Green	12	White/Brown