

TECHSPEC®

3" Dia, 6" FL Uncoated, Spherical Mirror



Stock **#32-826**

3-4 DAYS

-

1

+

**£162.35**

ADD TO CART

Qty 1-9

£162.35

Qty 10+

£137.70

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Substrate:

BOROFLAT®

Focal Length Tolerance (%):

±2

Surface Quality:

60-40

|                                                     |
|-----------------------------------------------------|
| <b>Surface Accuracy:</b><br>λ/4                     |
| <b>Diameter (inches):</b><br>3.0                    |
| <b>Diameter (mm):</b><br>76.20 +1.0/-0              |
| <b>Diameter Tolerance (inches):</b><br>+0.04/-0     |
| <b>Effective Focal Length EFL (inches):</b><br>6.00 |
| <b>Effective Focal Length EFL (mm):</b><br>152.40   |
| <b>Radius of Curvature (mm):</b><br>304.80          |
| <b>Aperture (f/#):</b><br>f/2                       |
| <b>Coating:</b><br>Uncoated                         |
| <b>Coating Type:</b><br>Uncoated                    |
| <b>Back Surface:</b><br>Ground                      |
| <b>Edge Thickness ET (inches):</b><br>0.50          |
| <b>Edge Thickness ET (mm):</b><br>12.70             |
| <b>Edge Thickness Tolerance (%):</b><br>+0.0/-15    |
| <b>Type:</b><br>Spherical Mirror                    |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |