

3" Travel, 5"L x 1.19"W Ball Bearing Slide



Linear Motion Ball Bearing Slides



Stock #37-364 3-4 DAYS

- 1 +

£232.90

ADD TO CART

Qty 1+

£232.90

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Ball Bearing

Type of Drive:
Manual

Type:

English
Stage Size (mm): 66.5 x 127.0
Travel (inches): 3
Construction: Aluminum Top and Base/440C Stainless Steel Bearings
Height (inches): 1.00
Load Capacity, Normal (lbs): 100
Mounting Threads: (6) 10-32 on Top
S.H.C.S. C'bore: (4) 1/4-20 on Base
Stage Size (inches): 2.62 x 5.00
Straight Line Accuracy (inches): 0.00008 per inch of travel
Weight (lbs): 1.1

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View