

TECHSPEC®

3X Arcturus® HeNe Beam Expander



3X HeNe Fixed Beam Expander, #58-208

Stock **#58-208** 3-4 DAYS



1



£378.25

ADD TO CART

Qty 1-4

£378.25

Qty 5+

£333.20

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
0

Coating:
BBAR (450-750nm)

Design Wavelength DWL (nm):
633

Entrance Aperture (mm): 2
Exit Aperture (mm): 27
Expansion Power: 3X
Focus Range: 1.2m - ∞
Substrate: ☐ Optical Glass
Length (mm): 115.00
Mounting Threads: C-Mount
Type: Beam Expander
Weight (g): 443
Housing Diameter (mm): 50
Transmitted Wavefront, P-V: <λ/4 @ 633nm for Input Beam ≤1mm
Coating Specification: R_{abs} <0.4% @ 630 - 670nm R_{avg} <0.6% @ 450 - 750nm
Wavelength Range (nm): 450 - 750
Style: Fixed Magnification
Divergence Adjustment: Non-Rotating Optics

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View