See all 21 Products in Family

4-10mm FL, CS-Mount, P-iris, 4K Motorized with Limit Switch

Image represents #22-806: Design will vary by stock number.

Stock **#22-809** **1 In Stock**

- 1 + **£382**.00

ADD TO CART

Volume Pricing	
Qty 1+	**£382.00** each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | Learn More

Product Downloads

General

Note:
User with Motorized Lens Control Board (#22-830)

Type:
Varifocal Lens

Physical & Mechanical Properties

Iris Option:
P-iris

Length (mm):
46.50

Maximum Diameter (mm):
59.0

Weight (g):
75

Optical Properties

Horizontal Field of View @ Max Sensor Format:
112° - 44°

Focal Length Range (mm):
4-10

Working Distance (mm):
500 - ∞

Aperture (f/#):
f/1.4 - Closed

Lens Wavelength Range:
VIS

Sensor

Maximum Sensor Format:
1/1.7"

Threading & Mounting

Mount:
CS-Mount

Regulatory Compliance

Certificate of Conformance:
View

Product Details

- 4 - 10mm Focal Length Range for up to 135° Horizontal FOV
- True 4K, 12 Megapixel Resolution
- IR corrected for Day or Night

4K Wide Angle Lenses provide a wide range of fields of view for applications with long working distance requirements, allowing for excellent resolution up to 12 megapixels. Available with DC auto-iris, P-iris, and manual iris versions, these lenses are ideal for a wide range of applications including Intelligent Traffic (ITS), remote sensing, security, and robotics. The lenses are IR corrected for use with true Day/Night cameras, providing a bright image in both visible and IR illumination without manual adjustment. Lens mounting options include S-mount (M12), CS-mount, and C-mount with motorized and non-motorized versions available.

;