

[See all 21 Products in Family](#)

## 4-10mm FL, CS-Mount, P-iris, 4K Ultra Motorized Zoom, Focus, Iris & IRC



Image represents #22-806: Design will vary by stock number.

Stock **#22-807** **1 In Stock**

⊖ 1 ⊕ £368<sup>00</sup>

**ADD TO CART**

### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1+     | £368.00 each                  |
| Need More? | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads

### General

**Note:**  
User with Motorized Lens Control Board (#22-830)

**Type:**  
Varifocal Lens

### Physical & Mechanical Properties

**Iris Option:**  
P-iris

|       |                               |
|-------|-------------------------------|
| 51.50 | <b>Length (mm):</b>           |
| 59.0  | <b>Maximum Diameter (mm):</b> |
| 74    | <b>Weight (g):</b>            |

## Optical Properties

|                |  |
|----------------|--|
| 112° - 44°     | <b>Horizontal Field of View @ Max Sensor Format:</b> |
| 4-10           | <b>Focal Length Range (mm):</b>                      |
| 500 - ∞        | <b>Working Distance (mm):</b>                        |
| f/1.4 - Closed | <b>Aperture (f/#):</b>                               |
| VIS            | <b>Lens Wavelength Range:</b>                        |

## Sensor

|        |                               |
|--------|-------------------------------|
| 1/1.7" | <b>Maximum Sensor Format:</b> |
|--------|-------------------------------|

## Threading & Mounting

|          |               |
|----------|---------------|
| CS-Mount | <b>Mount:</b> |
|----------|---------------|

## Regulatory Compliance

|                      |                                    |
|----------------------|------------------------------------|
| <a href="#">View</a> | <b>Certificate of Conformance:</b> |
|----------------------|------------------------------------|

## Product Details

- 4 - 10mm Focal Length Range for up to 135° Horizontal FOV
- True 4K, 12 Megapixel Resolution
- IR corrected for Day or Night

4K Wide Angle Lenses provide a wide range of fields of view for applications with long working distance requirements, allowing for excellent resolution up to 12 megapixels. Available with DC auto-iris, P-iris, and manual iris versions, these lenses are ideal for a wide range of applications including Intelligent Traffic (ITS), remote sensing, security, and robotics. The lenses are IR corrected for use with true Day/Night cameras, providing a bright image in both visible and IR illumination without manual adjustment. Lens mounting options include S-mount (M12), CS-mount, and C-mount with motorized and non-motorized versions available.