

**TECHSPEC® 40mm - 65mm Length, T-Mount Fine Focus Tube**



Stock #58-755 **20+ In Stock**

- 1 + £100.<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | £100.80 each                  |
| Qty 5-9        | £89.28 each                   |
| Qty 10-25      | £82.48 each                   |
| Need More?     | <a href="#">Request Quote</a> |

! Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Fine Focus Tube **Type:**

Extension Tube (Adjustable) **Function:**

**Physical & Mechanical Properties**

40.0 - 65.0 **Extension Length (mm):**

48.0                      **Outer Diameter (mm):**

33.0                      **Clear Aperture CA (mm):**

### Threading & Mounting

M33 x 0.5                      **Barrel Thread:**

T-Mount                      **Thread Type:**

### Regulatory Compliance

[Compliant](#)                      **RoHS 2015:**

[View](#)                      **Certificate of Conformance:**

[Compliant](#)                      **Reach 235:**

## Product Details

- Finely Threaded Internal Barrel for Fine Focus Adjustments
- Inner Diameter Baffle Thread for Stray Light Reduction
- Knurled Lip on Female End for Controlled Adjustments

TECHSPEC® C, S, and T-Mount Fine Thread Focus Tubes are used for making precision adjustments to optical element positions within a system. These tubes feature an outer barrel with male C, S, or T-Mount thread at the base end and a finely threaded interior barrel to allow for fine focusing. The secondary barrel has a female S, C, or T-Mount thread, knurled ring at the front end for easy adjustment, and a threaded interior for light baffle. Set screws can be used to fix the extension position. TECHSPEC C, S, and T-Mount Fine Thread Focus Tubes offer different extension length options to meet specific application demands.

**Note:** Compatible Allen wrenches for C, S, and T-Mount Fine Thread Focus Tubes ([#56-271](#), [#55-452](#), and [#58-637](#), respectively) sold separately.

## Technical Information

