

40 lp/mm, 1" x 3", Float Glass, Ronchi Ruling



Stock #38-260 CLEARANCE 2 In Stock

⊖ 1 ⊕ £169⁵⁶

ADD TO CART

Volume Pricing

Qty 1+	£169.56 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

Physical & Mechanical Properties

3.00 Length (inches):

12.7 x 25.4 Pattern Size (mm):

1.10 Thickness (mm):

1.00 Width (inches):

Optical Properties

Vacuum Deposited Chrome **Coating:**

40.00 **Frequency (lp/mm):**

Float Glass **Substrate:**

3.00 **Optical Density OD (Average):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 240:**

Product Details

- Used for Evaluation of Resolution, Field Distortion, and Parfocal Stability
- Ideal for Reticle and Field Calibration Requirements
- Available on Float Glass, Fused Silica, Fused Silica with Fluorescent Backing, and [Opal](#).

Precision Ronchi Ruling Glass slides are excellent for evaluating resolution, field distortion, and parfocal stability, especially of microscopes. Many different Linepairs Per Millimeter (lp/mm) versions available.