

4.0 OD M58 x 0.75, Machine Vision Absorptive ND Filter



Stock #21-739 1 In Stock

-

1

+

£125<sup>.60</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | £125.60 each                  |
| Qty 10+        | £119.20 each                  |
| Need More?     | <a href="#">Request Quote</a> |

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Mounted Imaging Filter

Type:

Physical & Mechanical Properties

53.00

Clear Aperture CA (mm):

Optical Properties

Optical Density OD (Average):

|                           |                                         |
|---------------------------|-----------------------------------------|
| 4.0                       |                                         |
| ND Filter Glass           | Substrate: <input type="checkbox"/>     |
|                           | Surface Quality:                        |
| 40-20                     |                                         |
|                           | Transmission (%):                       |
| 0.01                      |                                         |
|                           | Blocking Wavelength Range (nm):         |
| 425 - 675                 |                                         |
| Threading & Mounting      |                                         |
|                           | Filter Thread:                          |
| M58 x0.75                 |                                         |
|                           | Mount Thickness (mm):                   |
| 5.2                       |                                         |
|                           | Mount Thickness Including Threads (mm): |
| 7.0                       |                                         |
| Regulatory Compliance     |                                         |
|                           | Certificate of Conformance:             |
| <a href="#">View</a>      |                                         |
|                           | Reach 242:                              |
| <a href="#">Compliant</a> |                                         |

## Product Details

- Multiple Mounting Sizes and Threads Available
- 40-20 Surface Quality
- Helps Minimize Pixel Saturation

Machine Vision Absorptive Neutral Density (ND) Filters are designed to evenly attenuate the intensity of light over a specific wavelength range reaching a camera's sensor. These neutral density filters are spectrally flat in the visible spectrum from 425 – 675nm, so there is little to no effect on color balance. As such, these filters can be used with both monochromatic and color cameras. Machine Vision Absorptive Neutral Density (ND) Filters include both male and female threads, allowing them to be stacked with other neutral density filters to achieve various optical densities. Featuring common machine vision threads from M22 up to M105, these neutral density filters can be easily integrated into a wide variety of systems.