

TECHSPEC[®] 400-700nm OD 0.15, M25.5 x 0.5 Absorptive ND Filter



Stock #66-700 3-4 DAYS

-

1

+

£66.30

ADD TO CART

Qty 1-9
£66.30
Qty 10+
£61.88
Volume Pricing
Request Quote

ⓘ

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
28.00

Optical Density OD (Average):
0.15

Clear Aperture CA (mm):
22.0

Filter Thread:

M25.5 x 0.50
Substrate: ND Filter Glass
Coating: Uncoated
Transmission (%): 70.00
Type: Neutral Density Filter
Stock No. of Unmounted Filter: #46-211
Mount Thickness (mm): 9.9
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View