

TECHSPEC[®] 40mm, Side Drive, Standard Top, English Stage



40mm, Side Drive, Solid Top Stage

Stock #66-405 3-4 DAYS

-

1

+

£274.55

ADD TO CART

Qty 1-2

£274.55

Qty 3+

£239.61

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive:
Lead Screw

Drive Orientation: Side Drive
Type: English
Stage Size (mm): 40 x 40
Travel (inches): 0.5
Center Hole: 1/4-20
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 4
Mounting Threads: (1) 1/4-20, (4) 6-32, (8) 2-56
Stage Size (inches): 1.57 x 1.57
Straight Line Accuracy (µm): 2
Pitch (arcsec): 30
Yaw (arcsec): 25

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant