

40mm Sq. English Kinematic Magnetic Base



Stock #22-407 **9 In Stock**

⊖ 1 ⊕ £87²⁰

ADD TO CART

Volume Pricing

Qty 1-9	£87.20 each
Qty 10+	£79.04 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

English **Type:**
No **Switchable:**

Physical & Mechanical Properties

25.40 **Thickness (mm):**

40.00	Width (mm):
0.08	Weight (kg):
Anodized Aluminum	Construction:
40.00	Length (mm):
<70.0	Repeatability (µrad):

Threading & Mounting

(4) 2-56, (4) 6-32, (2) 8-32, (1) 1/4-20	Mounting Threads:
--	--------------------------

Material Properties

10	Magnetic Force (N):
----	----------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Common 25.4mm (1") Platform Height
- Removable Top Plates with High Repeatability Kinematic Positioning
- Compatible with all with [TECHSPEC Stages](#)

Kinematic Magnetic Base Plates are ideal for simplifying the adjustment of subsystems in a benchtop optical system. The bases feature a common platform height of 25.4mm (1") to allow for simplified optical axis alignment. Each base has a removeable top plate, ideal for adding or removing system components and subassemblies anywhere on a lab table with ease. Internal kinematic positioning allows the top plates to be removed and replaced with high repeatability. Kinematic Magnetic Base Plates are directly compatible with our [TECHSPEC stages](#), making them an ideal lab bench component for system building.