

## 40X Deluxe Illuminated Direct Measuring Microscope



Stock #55-678 **10 In Stock**

⊖ 1 ⊕ £444.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-4	£444.00 each
Qty 5+	£422.08 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

**Type of Illumination:**  
Adjustable & removable, battery operated

**Type of Focusing:**  
Rack and Pinion

**Note:**  
Magnification includes 10X Eyepiece

### Physical & Mechanical Properties

4.5 **Field of View (mm):**

0.02mm/0.001" **Increments:**

200.00 **Height (mm):**

0 - 3 **Reticle Scale (mm):**

0 - 0.10 **Reticle Scale (inches):**

580.00 **Weight (g):**

### Optical Properties

40X **Magnification:**

15.0 **Working Distance (mm):**

### Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

Reticle cannot and should not be removed or replaced.

- 40X and 100X Models, Include 10X Eyepiece
- Inch/Metric Reticle
- Rack and Pinion Focusing

For quick and precise measurements in laboratories, workshops and assembly lines. Features a dual scale reticle graduated in both inches and millimeters. A turn of the eyepiece brings the reticle into sharp focus. Vertical adjustment knob sharpens the subject image. Includes a fully vertically adjustable battery operated penlight illuminator, which can be removed for use elsewhere. Scope has cutaway opening at base for subject manipulation.

**Note:** Reticle cannot and should not be removed or replaced.