

40X Deluxe Illuminated Direct Measuring Microscope



Stock **#55-678** [CONTACT US](#)

-

1

+

£444^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	£444.00 each
Qty 5+	£422.08 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type of Illumination:

Adjustable & removable, battery operated

Type of Focusing:

Rack and Pinion

Note:

Magnification includes 10XEyepiece

Physical & Mechanical Properties

4.5	Field of View (mm):
0.02mm/0.001"	Increments:
200.00	Height (mm):
0 - 3	Reticle Scale (mm):
0 - 0.10	Reticle Scale (inches):
580.00	Weight (g):

Optical Properties

40X	Magnification:
15.0	Working Distance (mm):

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

Reticle cannot and should not be removed or replaced.

- 40Xand 100XModels, Include 10XEyepiece
- Inch/Metric Reticle
- Rack and Pinion Focusing

For quick and precise measurements in laboratories, workshops and assembly lines. Features a dual scale reticle graduated in both inches and millimeters. A turn of the eyepiece brings the reticle into sharp focus. Vertical adjustment knob sharpens the subject image. Includes a fully vertically adjustable battery operated penlight illuminator, which can be removed for use elsewhere. Scope has cutaway opening at base for subject manipulation.

Note: Reticle cannot and should not be removed or replaced.