

TECHSPEC®

4.25" Diameter x 34" FL Protected Aluminum, Parabolic Mirror



Stock #32-067-522 [CONTACT US](#)

-

1

+

£370.60

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| £370.60                       |
| Qty 10+                       |
| £315.35                       |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: 

BOROFLOAT®

Focal Length Tolerance (%):  
±1.5

Surface Quality:  
60-40

Surface Accuracy:

|                                                                                                                                                                         |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| N/8                                                                                                                                                                     |
| <b>Diameter (inches):</b><br>4.25 +0.06/-0                                                                                                                              |
| <b>Diameter (mm):</b><br>108.00 +1.5/-0                                                                                                                                 |
| <b>Effective Focal Length EFL (inches):</b><br>34.0                                                                                                                     |
| <b>Effective Focal Length EFL (mm):</b><br>863.60                                                                                                                       |
| <b>Radius of Curvature (mm):</b><br>1,727.20                                                                                                                            |
| <b>Aperture (f/#):</b><br>f/8                                                                                                                                           |
| <b>Coating:</b><br>Protected Aluminum (400-2000nm)                                                                                                                      |
| <b>Coating Specification:</b><br>R <sub>avg</sub> >85% @ 400 - 700nm<br>R <sub>avg</sub> >90% @ 400 - 2000nm                                                            |
| <b>Coating Type:</b><br>Metal                                                                                                                                           |
| <b>Back Surface:</b><br>Ground                                                                                                                                          |
| <b>Clear Aperture CA (mm):</b><br>98                                                                                                                                    |
| <b>Edge Thickness ET (inches):</b><br>0.75                                                                                                                              |
| <b>Edge Thickness ET (mm):</b><br>19.10                                                                                                                                 |
| <b>Type:</b><br>Parabolic Mirror                                                                                                                                        |
| <b>Wavelength Range (µm):</b><br>0.4 - 2                                                                                                                                |
| <b>Wavelength Range (nm):</b><br>400 - 2000                                                                                                                             |
| <b>Damage Threshold, Reference:</b> <br>0.3 J/cm <sup>2</sup> @ 532nm & 1064nm, 10ns |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |