

TECHSPEC[®] 4.25" Dia. x 45" FL Prot. Alum., Spherical Mirror



Stock #50-051 3-4 DAYS

-

1

+

£481.95

ADD TO CART

Qty 1-9
£481.95
Qty 10+
£409.70
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Substrate:

BOROFLAT[®]

Focal Length Tolerance (%):
±2

Surface Quality:
60-40

Surface Accuracy: λ/8
Diameter (inches): 4.25
Diameter (mm): 107.95 +0.5/-0
Diameter Tolerance (inches): +0.02/-0
Effective Focal Length EFL (inches): 45.0
Effective Focal Length EFL (mm): 1,143.00
Radius of Curvature (mm): 2,286.00
Aperture (f/#): f/10.6
Coating: Protected Aluminum (400-2000nm)
Coating Specification: R _{avg} >85% @ 400 - 700nm R _{avg} >90% @ 400 - 2000nm
Coating Type: Metal
Back Surface: Ground
Edge Thickness ET (inches): 0.75
Edge Thickness ET (mm): 19.05
Edge Thickness Tolerance (%): +0.0/-10
Type: Spherical Mirror
Wavelength Range (nm): 400 - 2000
Damage Threshold, Reference: ☐ 0.3 J/cm ² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant