

4.4-11mm FL High Resolution Varifocal Lens



#68-665

Stock #68-665 **5 In Stock**

⊖ 1 ⊕ £465.⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	£465.00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Low Distortion **Note:**
Varifocal Lens **Type:**

Physical & Mechanical Properties

56.50 **Length (mm):**
Weight (g):

125.00

45.00 Diameter (mm):

Optical Properties

Field of View @ Min Working Distance (mm):
400 - 175

Horizontal Field of View, 1/2" Sensor:
68.1° - 32.6°

4.4-11 Focal Length Range (mm):

300 - ∞ Working Distance (mm):

f/1.6 - f/16 Aperture (f#):

VS Lens Wavelength Range:

Sensor

1/1.8" Maximum Sensor Format:

Threading & Mounting

M43 x 0.75 Filter Thread:

C-Mount Mount:

Regulatory Compliance

[Exempt](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Contains SVHC\(s\)](#) REACH 241:

Product Details

CS-Mount lenses are not compatible with C-Mount cameras.

- Low Distortion and Day/Night Options
- Focal Lengths from 4.4mm - 90mm
- C-Mount Versions

Megapixel Varifocal Lenses are the ideal choice when you need a specific field of view that corresponds to a non-standard focal length. They make system integration straightforward while allowing for fine tuning, and also create the flexibility so the lenses can be integrated across multiple applications. Day/Night varifocal lenses are the perfect choice when you need to extend your imaging system into the NIR without sacrificing visible imaging. Megapixel Varifocal Lenses have C-Mount versions. The lenses feature focal lengths from 4.4 to 90mm.