

45° 2.5mm Output Dia., Molded Compound Parabolic Concentrator



Molded Compound Parabolic Concentrators (CPCs)



Stock **#17-709** ☐ In Stock



1



£112.20

ADD TO CART

Qty 1-5
£112.20
Qty 6+
£89.67
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: ☐ [E270](#)

Coating:
Uncoated

Type: Specialty Lens
Wavelength Range (nm): 350 - 2500
Input Diameter (mm): 5.39
Length (mm): 10.52 ±0.10
Outer Diameter (mm): 11.00 ±0.20
Output Diameter (mm): 2.50
Surface Quality: 80-50
Acceptance Angle (°): 45

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View