

450nm CWL, 80nm FWHM, 12.7mm Mounted Diameter



Bandpass Interference Filters

Stock **#62-797** CLEARANCE 3-4 DAYS

-

1

+

£16.11

ADD TO CART

Qty 1+

£16.11

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.70

Optical Density OD (Average):
≥3.0

Center Wavelength CWL (nm):
450.00

Center Wavelength CWL Tolerance (nm):
±15

Full Width-Half Max FWHM (nm):

80.00
Full Width-Half Max FWHM Tolerance (nm): ±25
Minimum Transmission (%): 60.00
Operating Temperature (°C): -50 to +75
Coating: Traditional Coated
Surface Quality: 80-50
Type: Bandpass Filter
Blocking Wavelength Range (nm): 200 - 1200
Angle Sensitivity: Intended for Collimated Input
Mount Thickness (mm): 9.6

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View