

46mm Diameter Unmounted, Linear Glass Polarizing Filter



Stock #53-347

3-4 DAYS

-

1

+

£38.25

ADD TO CART

Qty 1-5
£38.25
Qty 6+
£29.75
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
46.00

Extinction Ratio:
100:1

Substrate:
Polymer Film on [B270](#)

Operating Temperature (°C): -15 to +70
Surface Quality: 80-50
Thickness (mm): 2.40
Thickness Tolerance (mm): ±0.2
Transmission (%): Single: ~30
Type: Linear Polarizer
Parallelism (arcmin): <3
Dimensional Tolerance (mm): +0.0/-0.2
Bevel: Protective bevel as needed
Construction: Dichroic Polarizing Film on Glass
Edges: Cut
Wavelength Range (nm): 400 - 700
Surface Flatness (P-V): 4 - 6λ
Polarization Efficiency (%): 95

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View