

4.7mm Focal Length Lens, 1" Sensor Format



4.7mm Focal Length Lens, 1" Sensor Format

Stock #75-217 **NEW** **2 In Stock**

⊖ 1 ⊕ £1,275⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	£1,275.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Product Family:
1" Format Fixed Focal Length Lenses

Type:
Fixed Focal Length Lens

Physical & Mechanical Properties

Iris Option:
Variable

Length (mm):

64.70

Maximum Diameter (mm):

71.0

Weight (g):

360

Optical Properties

Horizontal Field of View, 1" Sensor:

112.2°

Maximum Image Circle (mm):

16.00

TV Distortion (%):

-0.58

Focal Length FL (mm):

4.70

Working Distance (mm):

100 - ∞

Aperture (f#):

f/2.4 - f/11

Maximum Distortion (%):

-0.58

Lens Wavelength Range:

VS

Wavelength:

VS

Sensor

Maximum Sensor Format:

1"

Pixel Size (µm):

5.00

Threading & Mounting

Filter Thread:

None

Mount:

C-Mount

Regulatory Compliance

Certificate of Conformance:


[View](#)

Product Details


- Up to 1", C-Mount Lens
- "Fast" Lenses for Increased Throughput
- 4.7mm to 75mm Focal Length

1" Format Fixed Focal Length Lenses provide high throughput and high resolution across the entire camera sensor, allowing for excellent imaging even in less-than-ideal lighting conditions. Offered in 9 focal lengths from 4.7mm to 75mm, this complete family covers many of the applications in the market today. Engineered to minimize distortion, these lenses provide a perfect image for a human operator or an automated system. 1" Format Fixed Focal Length Lenses also feature a standard C-Mount lens mount for easy integration with the most common machine vision [cameras](#) we offer. All lenses feature front filter threading to attach to your choice of [optical filter](#).


Technical Information




#75-217, 4.7mm Focal Length Lens, 1" Sensor Format, Transmission Plot



#75-217, 4.7mm Focal Length Lens, 1" Sensor Format, Relative Illumination Plot



#75-217, 4.7mm Focal Length Lens, 1" Sensor Format, MTF Plot



#75-217, 4.7mm Focal Length Lens, 1" Sensor Format, Distortion Plot