

4" x 4" (100 lp/inch), Ronchi Ruling



Stock **#56-619** 3-4 DAYS

- 1 + **£365.50**

ADD TO CART

Qty 1-4
£365.50

Qty 5+
£347.31

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating:
Vacuum Deposited Chrome, OD >3.0

Dimensional Tolerance (inches):
±0.02

Substrate:
Float Glass

Optical Density OD (Average):

3.00
Dimensions (inches): 4 x4
Surface Quality: 60-40
Thickness (mm): 1.50
Type: English
Parallelism (arcmin): ±60
Dimensional Tolerance (mm): ± 0.02
Frequency (lp/inch): 100.00
Line to Line Parallelism (arcsec): ≤2
Parallelism of Pattern to Substrate (°): ±1
Surface Flatness (P-V): 1λ

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View