

4X Objective, Nikon CFI Plan Fluor

See More by [Nikon](#)



4X Objective, Nikon CFI Plan Fluor, #88-378

Stock **#88-378** **2 In Stock**

-

1

+

£448^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	£448.00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
	Model Number:
MRH00045	
	Compatible Tube Lens Focal Length (mm):
Focal Length: 200mm	
	Type:
Microscope Objective	
	Style:
Infinity Corrected	


Manufacturer:		Nikon
Physical & Mechanical Properties		
Field of View (mm):		6.25
Length excluding Threads (mm):		42.70
Maximum Diameter (mm):		30
Weight (g):		140.00
Optical Properties		
Compatible Cover Glass Thickness (mm):		N/A
Horizontal Field of View, 1/2" Sensor:		1.60mm
Horizontal Field of View, 2/3" Sensor:		2.20mm
Magnification:		4X
Numerical Aperture NA:		0.13
Working Distance (mm):		17.2
Field Number (mm):		25
Parfocal Length (mm):		59.9
Immersion Liquid:		N/A
Sensor		
Maximum Sensor Format:		2/3"
Threading & Mounting		
Mounting Threads:		M25 x 0.75
Regulatory Compliance		
RoHS 2015:		Exempt
Certificate of Conformance:		View
Reach 235:		Contains SVHC(s)

Product Details

- Provide High Contrast Fluorescence Observation
- Ideal for Multiple Microscopy Techniques
- High Transmission from UV to the IR

Nikon CFI Plan Fluor Objectives feature high transmission from the ultraviolet to the infrared, along with exceptional flatness across the entire field of view. These objectives are ideal multipurpose objectives for a variety of microscopy techniques, including brightfield, fluorescence, polarizing, or DIC microscopy. These microscope objectives are suitable for high contrast fluorescence observation or for applications including photomicrography. Nikon CFI Plan Fluor Objectives have M25 x 0.75 mounting threads. The objectives are available in magnifications from 4X up to 60X.

Technical Information



Dimensions (mm)								
Stock No.	Nikon Model Number	Immersion Liquid	Magnification	Parafocal Length	A	B	C	D
#88-378	MRH00041	N/A	4X	60.06	30.0	42.7	16.5	M25 x0.75
#88-379	MRH00101	N/A	10X	60.06	30.0	42.4	18.0	M25 x0.75
#38-004	MRP07220	Water	16X	75.0	35.0	72.0	6.0	M32 x0.75
#88-380	MRH00201	N/A	20X	60.06	28.0	57.8	8.5	M25 x0.75
#88-381	MRH00405	N/A	40X	60.06	30.0	59.2	10.0	M25 x0.75
#88-382	MRH00602	N/A	60X	60.06	31.5	59.2	5.0	M25 x0.75