


TECHSPEC[®] 5 x 5mm, 0.25 Numerical Aperture, Uncoated, Square Precision Aspheric Lens



Stock #17-304 CLEARANCE 3-4 DAYS

-

1

+

£182.75

ADD TO CART

Qty 1-5
£182.75
Qty 6+
£146.20
Volume Pricing
Request Quote

ⓘ

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
5.00 x 5.00

Effective Focal Length EFL (mm):
10.00 @ 587.6nm

Numerical Aperture NA:
0.25

Back Focal Length BFL (mm): 5.68
Substrate: N-SF6
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: Uncoated
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 4.50 x4.50
Edge Thickness ET (mm): 7.41
Center Thickness CT (mm): 7.80 ±0.10
f#: 2.00
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 390 - 2500
Conjugate Distance: Infinite
Power (diopters): 100.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View