

50 x 50mm 120 Grit Ground Glass Diffuser



Stock #83-382 3-4 DAYS

-

1

+

£19.97

ADD TO CART

Qty 1-10
£19.97
Qty 11+
£17.43
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating: Uncoated
Dimensional Tolerance (mm): ±0.25
Dimensions (mm): 50.00 x 50.00
Edges:

Cut Edges
Grit: 120
Substrate: Float Glass
Thickness (mm):1.60
Type:Ground Glass Diffuser
Wavelength Range (nm):350 - 2000
Width (mm):50.00
Note:Sandblasted on first surface
Length (mm):50.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant