

50 x 75mm, Blue, EuroBrite™ Spot Light

See More by [Advanced Illumination](#)



Blue AI EuroBrite Spot Light

Stock **#33-452** [CONTACT US](#)

-

1

+

£260.00

ADD TO CART

Volume Pricing	
Qty 1+	£260.00 each
Need More?	Request Quote

ⓘ

 Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General	
50,000	Operating Lifetime (hours):
SL-S050075M470	Model Number:
LED Illuminator	Type of Illumination:

Note: See Technical Information Tab for Typical Intensity	
Advanced Illumination	Manufacturer:
Spot Light	Geometry:

Strobed or Constant	Illumination Mode:
---------------------	---------------------------

Physical & Mechanical Properties

75 x 89 x 30	Dimensions (mm):
97.00	Weight (g):

50 x 75	Active Area (mm):
---------	--------------------------

Optical Properties

Blue	Color:
470	Wavelength (nm):

Electrical

0.42 - 0.49A	Maximum Input Current:
10% @ 0.7V, 100% @ 10V	Analog Intensity Control:

10µm	Trigger-to-Pulse Latency:
------	----------------------------------

Hardware & Interface Connectivity

Flying Leads	Connector:
24V nominal (min. 22 / max. 28)	Input Voltage (V):

Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	
---	--

Environmental & Durability Factors

0 - 60	Operating Temperature (°C):
IP67	Environmental Rating:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:

Contains SVHC(s)	Reach 233:
----------------------------------	-------------------

Product Details

- DaisyChain up to Four 100 x 150mm Units
- Requires No Heat Sink
- Available in White, Red, and Blue

Advanced Illumination EuroBrite™ Spot Light illuminators feature on-board smart drivers functional during strobe and continuous operation modes making them ideal for the most demanding performance constraints. Adaptive OverDrive™ allows for power optimization while in strobing mode, and Adaptive Thermal Feedback™ gives operational current control to the user, preventing overheating and eliminating the need for a heat sink. These Advanced Illumination EuroBrite™ Spot Light illuminators feature a ruggedized, sealed enclosure, and are available in white, red, or blue versions. The ability to operate four 100 x 150mm units connected to one another, and an analog dimming control operable in both strobe and continuous modes add to illuminator’s customizability.

Note: A 24V power supply is required.

Technical Information

Typical Intensity				
Size	50 x 75mm	50 x 75mm	50 x 75mm	100 x 150mm

Working Distance	100mm	300mm	600mm	600mm
Area	79 x 56mm	117 x 99mm	ø198mm	325 x 198mm
Typical Irradiance (W/M²)	100.0	74	28	147
Typical Illuminance (kLux)	34.0	25	10	49