

50.0mm FL, No IR-Cut Filter, f/2.5, Micro Video Lens



Stock **#59-781** ☐ In Stock

-

1

+

£62.90

ADD TO CART

Qty 1-49
£62.90
Qty 50+
£48.45
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
52.80

Filter Thread:
M12 x0.50

Maximum Diameter (mm):
27.0

Maximum Image Circle (mm):

8.00
Horizontal Field of View @ Max Sensor Format: 6.8
Resolution, On-Axis: 160 lp/mm @ 20% Contrast
Resolution, 0.7 Field: 100 lp/mm @ 20% Contrast
Resolution, Full Field: 80 lp/mm @ 20% Contrast
Note: Standard
Type: M12 Imaging Lens
Focal Length FL (mm): 50.00
Maximum Sensor Format: 1/2"
Working Distance (mm): 400 - ∞
Mount: M12 x 0.5 (S-Mount)
Aperture (f/#): f/2.5
Distortion (%): -1.20 @ Full Field
IR Cut Filter: No
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View