

## 500mm Neck, Flood Lamp



Stock #58-078 [CONTACT US](#)

- 1 + £129.<sup>00</sup>

[ADD TO CART](#)

### Volume Pricing

Qty 1+	£129.00 each
Need More?	<a href="#">Request Quote</a>

Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

Type of Illumination:  
Fiber Optic Illuminator, Incandescent

Geometry:  
Spot Light

Illumination Mode:  
Constant

#### Optical Properties

Color:  
White

---

## Regulatory Compliance

Certificate of Conformance:

[View](#)

---

## Product Details

Gooseneck quartz halogen illuminators feature a 12V/20W Halogen bulb housed in a high impact, polyamide housing. A heat dissipating Dichroic reflector and clear lens provide a wide angle illumination (flood) or a narrow spot. The lamphead is mounted on a 700 or 500mm gooseneck arm that easily adjusts to any angle. Lamps can be secured directly to a bench or can be mounted on a table top base or an adjustable C-clamp, listed below.

---

;