

500mm Neck, Flood Lamp



Stock **#58-078** 1 In Stock

-

1

+

£129^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	£129.00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Type of Illumination:	Fiber Optic Illuminator, Incondescent
Geometry:	Spot Light
Illumination Mode:	Constant
Optical Properties	
Color:	White

Regulatory Compliance

[View](#)

Certificate of Conformance:

Product Details

Gooseneck quartz halogen illuminators feature a 12V/20W Halogen bulb housed in a high impact, polyamide housing. A heat dissipating Dichroic reflector and clear lens provide a wide angle illumination (flood) or a narrow spot. The lamphead is mounted on a 700 or 500mm gooseneck arm that easily adjusts to any angle. Lamps can be secured directly to a bench or can be mounted on a table top base or an adjustable C-clamp, listed below.

;