

500mm Neck, Spot Lamp



Stock #58-076 [CONTACT US](#)

- 1 + £127^{.50}

ADD TO CART

Volume Pricing

Qty 1+	£127.50 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type of Illumination:
Fiber Optic Illuminator, Incandescent

Geometry:
Spot Light

Illumination Mode:
Constant

Optical Properties

Color:
White

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

Gooseneck quartz halogen illuminators feature a 12V/20W Halogen bulb housed in a high impact, polyamide housing. A heat dissipating Dichroic reflector and clear lens provide a wide angle illumination (flood) or a narrow spot. The lamphead is mounted on a 700 or 500mm gooseneck arm that easily adjusts to any angle. Lamps can be secured directly to a bench or can be mounted on a table top base or an adjustable C-clamp, listed below.

;