


50/50.8mm Dia., Kinematic Mount, 3-Screws, Quick Start Optical Mounts



50/50.8mm Diameter Kinematic Mount, 3-Screws , #58-855



Stock **#17-524** [CONTACT US](#)

- 1 +

£163.45

ADD TO CART

Qty 1+
£163.45

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Adjustable - Tip-Tilt

Type of Optics:
Circular

Size of Compatible Optics (mm):
50.0 - 50.8

Number of Adjustment Screws:

Clear Aperture CA (mm): 45.9
Travel (mm): Z-Axis: 12
Construction: Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings
Angle Tolerance (°): 0.2 per 0.25mm turn
Fine Tilt Angle (°): ±5
Fine Tip Angle (°): ±5
Sensitivity per 1° Knob Rotation (arcsec): 2.3
Thermal Stability (μrad): <5
Adjustment Screw Pitch (mm): 0.25
Contents of Kit: #58-855 , #15-857 , #15-845
Compatible Post: M4 x0.7, 8-32
Min. Thickness of Compatible Optics (mm): 2.0
Pointing Stability (μrad): 1.3
Optical Axis Height (mm): 127.00
Post Diameter (mm): 25.4

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View