

50.8mm Dia. x 50.8mm FL, Uncoated, ZnSe Aspheric Lens



Stock #62-963 3-4 DAYS

-

1

+

£1,187.45

ADD TO CART

Qty 1+
£1,187.45

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.80 +0.0/-0.13

Effective Focal Length EFL (mm):
50.80 @ 10600nm

Numerical Aperture NA:
0.50

Substrate: ☐
Zinc Selenide (ZnSe)

Aspheric Design Wavelength (nm): 10600
Coating: Uncoated
Centering (arcmin): ≤3
Surface Quality: 60-40
Clear Aperture CA (mm): 45.72
Edge Thickness ET (mm): 3.10
Center Thickness CT (mm): 8.30 ±0.20
f#: 1.00
Bevel: Protective bevel as needed
Type: Aspheric Lens
Wavelength Range (nm): 600 - 18000
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View
